







INSTALLATION GUIDE – ERGO HANDLE CENTRAL LOCKING KIT

PART NUMBER	DESCRIPTION	QTY	
P1-28630-RPK-J2**-35	Eberhard Ergo Whale Tail Compression Handle T-Handle, Stamp Black/ Chrome Key J2** Padlockable 1.32 Inch Cam	1	
P1-28630-RSS-J2**-03	Eberhard Ergo Whale Tail Compression Handle T-Handle, Stamp Stainless Steel/ Chrome Key J2** Padlockable 1.32 Inch Cam	1	
P-28630-RPK-J2**-42	Eberhard Ergo Whale Tail Compression Handle T-Handle, Stamp Black/ Black Key J2** Padlockable 0.85 Inch Cam	1	
Included with handles	Keys	2	



129566	Nylock Nut P-Type HEX 10-24 UNC IMP Included with black & chrome or black & black handles. NOT included with stainless steel handle.	4	
CLLH-0678-3	ERGO Aluminium Bracket Includes 3 self-tapping screws.	1	
RADN/ RA24	Power door slave actuator with spring detent. Nose end fitting. Available in 12V (RADN) or 24V (RA24).	1	
CP-ADAPTER-PIN	Adapter Pin 8mm x 25mm	1	
HAIR-4	Hair Pin Cotter 1/4" - 3/8"	1	




Additional Extras Available:

18400-P5-25	Additional Washers & Cotter Pins	1	
9301-B-1200	ROD WITH ROLLER 8mm X 1200mm (Single)	1	
9301-C-1200	ROD 8mm X 1200mm (Single)	1	
3P-24A	RODS 3/8IN - 3 PT - 1200MM - #199-1 (PAIR)	2	
H-68	ROD ROLLER (199-7) – 1/D9.5mm (PAIR) To be used with 3P-24A	2	

INSTALLATION

STEP 1


Install the Eberhard Ergo Handle to the surface of the panel by securing the top 2 mounting holes with the nylocks.



STEP 2


Attach the CP-Adapter Pin to the Lock Cam, fixing with the HAIR-4 clip. Place the "D" nose of the Actuator over the Pin.





STEP 3

Insert the aluminium bracket over the bottom 2 mounting and secure with the remaining 2 nylocks.



STEP 4

Secure the RADN actuator to the aluminium bracket with the self-tapping screws.

